UNDERCOUNTER GLASSWASHERS AUTOMATIC ROTARY

Perlick Features

- Cleans and sanitizes up to 1000 2¹/₂" glasses per hour.
- Hands-free glass activated on/off stop is safe and convenient.
- Independent upper and lower wash and rinse arms ensure superior results.
- 120V with built-in 1.25kw electric tank heater maintains the recirculated wash water to the recommended 140°F wash temperature.
- Compatible with both iodine and chlorine sanitizers.
- Simple controls for operation and cleaning.
- All stainless steel construction assures trouble free service and a long life.
- Adjustable rinse temperature allows flexible sanitizing options.
- Poly Pro[™] circular conveyor is extremely durable and reduces chipping and breakage of glassware.
- Double wall construction for quiet back bar operation.
- Internal chemical storage.
- Built-in chemical pumps with primer switches.

MODEL NOS.

□ PKC24









Sizes and Specifications — PKC24 Undercounter Glasswasher Automatic Rotary


| Job | | |
|-----------|------|--|
| Area | | |
| Item No | | |
| Model No. | | |







| | · · | | | |
|------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------|--|--|
| MODEL NOS. | | PKC24 | | |
| CABINET DIMENSIONS | Length - Inches (mm) | 251/4" (641) | | |
| | Depth - Inches (mm) | 25 ¹ /8" (638) | | |
| | Height - Inches (mm) | 39"— 401/2" (990-1028) | | |
| MAX CLEARANCE FOR GLASSWARE | | 11 ³ / ₄ (298.4mm) | | |
| OPERATING CAPACITY | | 1000 (2 ¹ /2") glasses per hour | | |
| OPERATING TEMPERATURES | | Inlet water (hot) recommended 140°F (60°C). Inlet water (cold) 75°F (24°C) | | |
| WATER CONSUMPTION | | Hot water (initial fill) 3 Gal. (11.25 L). Hot water per hour (max.) 12 Gal. (45.42 L). Cold water per minute (approximately) 28 GPM (10.6 LPM). | | |
| WATER REQUIREMENTS | | Hor water inlet 1/2" (12.7mm). Cold water inlet 1/2" (12.7mm). Drain (Max.) 11/2" (38.1mm) | | |
| DRAIN FLOW (gals. per hour) | | Continuous operation: Max. 180 GPH | | |
| EXHAUST REQUIREMENTS | | None | | |
| ELECTRICAL RATING | | 120/60/1 Volts — 11 Amps | | |
| TANK HEATER | | 1.25kw | | |
| SHIP WT lbs. (kg) | | 156 (71) | | |
| PLUMBING | Hot and Cold Water Inlet Connection: 1/2" NPT. Incoming Hot Water: 120° F, at 30-60 PSI. Incoming Cold Water: 75° F at 30-60 PSI. Drain: 11/2" tale piece. | | | |
| WATER HARNESS | Water containing more than 15 GPG will require a water softener. Caution: Parts failure caused by hard water are not covered under Perlick's warranty. | | | |
| DETERGENT, SANITIZER and RINSE AID | Detergent : A heavy-duty liquid warewashing detergent containing water conditioners. Chlorine Sanitizer : Any EPA registered chlorine can be used. The EPA marking can be found on the container label. Rinse Aid : A low-foaming warewashing rinse aid containing water conditioners. Note : <i>To ensure maximum glasswasher performance. It is important to select the appropriate detergent and rinse aid for specific water conditions. These chemicals can be purchased from a local chemical supplier or food service distributor.</i> | | | |
| SUMMARY SPECIFICATIONS | The PKC24 glasswasher is designed to produce sparkling clean glassware utilizing separate detergent, sanitizer and rinse aid chemical pumps. Standard features include upper and lower wash/rinse arms, wash tank heater, Poly Pro™ conveyor, splash curtains, double-walled construction, and storage space for three 1-gallon containers. The PKC24 isconstructed for extended life out of stainless steel. | | | |





8300 West Good Hope Road • Milwaukee, WI 53223 • Phone 414-353-7060 • Fax 414-353-7069 Toll Free 800-558-5592 • E-Mail: Perlick@Perlick.com • www.Perlick.com